



M1500 SECOND STEP

Application and Specifications

Application

Wash your marine vessel properly, prior to the polishing process. Use appropriate tools (polishing machine, pad etc.) compatible with M1500.

Wipe the polish residue with a lint-free microfiber cloth. Always remove excess polish and do not let dry. Do not use at high speed. It is suitable for rotary and orbital machines.

Specifications

Packaging	1 kg
Application Temperature	5°C-30°C
Sanding Level	P1500
Cutting Level	Fine
Gloss Rate	%60